




Installation Axessline Terminal Power Strip : 935-T4DC


1




OR



2



Cable L = 0,3 m



Ext. cable not included



Ext. cable not included



Ext. cable not included



Ext. cable not included



Ext. cable not included

WIELAND GST18I3S Female type
Part no 92.931.3053.1
VDE Approval no. 40018414


Cable cord specification
H05VV-F according to EN 50525-2-11
minimum 3 x 1.5 mm²




Accessories
Wieland <-> Schuko
1.5 m 935-BA15
3.0 m 935-BA30
5.0 m 935-BA50

Recommended Accessories

935-TA50 TopAccess Conference Outlet Box



935-C093 Allround Cable Tray



Considerations when using HDMI.

Usually, you should not exceed a length of 8-10 meters for good signal! Amplifiers should be used at longer installations! There are many factors that affect the signal - the cables quality, contacts, amount of data (resolution) and source strength.